



(https://bestamada.com/wp-content/uploads/2021/08/详情Detail-2.png)


(https://bestamada.com/wp-content/uploads/2021/08/主图Main-1.jpg)



9 Inch 2M CMOS Display Camera HD LCD

- Click the button to directly record and shoot 1080P&30FPS video, the file is stored in the built-in hard disk, can also be extended to an external TF. operation to make it easy to use.
- After turning on the camera, menu will show up
Click and play!





SEARCH INQUIRY ([HTTPS://BESTAMADA.COM/CONTACT/](https://bestamada.com/contact/))

Category: LCD Screen (<https://bestamada.com/product-category/microscope-accessory/lcd-screen/>)

Description

Description

Model	AM090
Series	Integrated display camera
Sensor size	1/3"
Effective pixels	Full HD
Resolution	1024*600@30FPS
Output	USB2.0, TF card (Synchronized output with the screen)
Pixel size	2.75*2.75µm
Power	DC-12V/1A
Size	225.00*52.04*175.00mm
Weight	0.7kg
Accessory	USB2.0 Cable, Mouse, DC-12V Power adapter

RELATED PRODUCTS



[\(https://bestamada.com/product/16m-windows-10-tablet-integrated-display-camera/\)](https://bestamada.com/product/16m-windows-10-tablet-integrated-display-camera/)

16M Windows 10 Tablet Display Camera

[\(https://bestamada.com/product/16m-windows-10-tablet-integrated-display-camera/\)](https://bestamada.com/product/16m-windows-10-tablet-integrated-display-camera/)



[\(https://bestamada.com/product/5m-android-9-7-inch-retina-lcd-screen/\)](https://bestamada.com/product/5m-android-9-7-inch-retina-lcd-screen/)

5M Android 9.7 inch Retina LCD Screen

[\(https://bestamada.com/product/5m-android-9-7-inch-retina-lcd-screen/\)](https://bestamada.com/product/5m-android-9-7-inch-retina-lcd-screen/)



[\(https://bestamada.com/product/11-6-inch-lcd-screen-with-panasonic-sensor/\)](https://bestamada.com/product/11-6-inch-lcd-screen-with-panasonic-sensor/)

11.6 Inch LCD Screen with Panasonic Sensor

[\(https://bestamada.com/product/11-6-inch-lcd-screen-with-panasonic-sensor/\)](https://bestamada.com/product/11-6-inch-lcd-screen-with-panasonic-sensor/)

How can I help you?



NAVIGATION MENU

- [Home \(https://bestamada.com/\)](https://bestamada.com/)
- [Products \(https://bestamada.com/products/\)](https://bestamada.com/products/)
- [About Us \(https://bestamada.com/about/\)](https://bestamada.com/about/)
- [FAQ \(https://bestamada.com/faq/\)](https://bestamada.com/faq/)
- [Contact Us \(https://bestamada.com/contact/\)](https://bestamada.com/contact/)

PRODUCT CATEGORIES

- [Biological Microscope \(https://bestamada.com/product-category/biological-microscope/\)](https://bestamada.com/product-category/biological-microscope/) ▼
- [Zoom Monocular Microscope \(https://bestamada.com/product-category/zoom-monocular-microscope/\)](https://bestamada.com/product-category/zoom-monocular-microscope/) ▼
- [Zoom Stereo Microscope \(https://bestamada.com/product-category/stereo-microscope/\)](https://bestamada.com/product-category/stereo-microscope/) ▼
- [Industrial Microscope \(https://bestamada.com/product-category/industrial-microscope/\)](https://bestamada.com/product-category/industrial-microscope/)
- [Fluorescence Microscope \(https://bestamada.com/product-category/fluorescence-microscope/\)](https://bestamada.com/product-category/fluorescence-microscope/) ▼
- [Metallurgical Microscope \(https://bestamada.com/product-category/metallurgical-microscope/\)](https://bestamada.com/product-category/metallurgical-microscope/) ▼
- [Polarizing Microscope \(https://bestamada.com/product-category/polarizing-microscope/\)](https://bestamada.com/product-category/polarizing-microscope/) ▼
- [Video Digital Microscope \(https://bestamada.com/product-category/video-digital-microscope/\)](https://bestamada.com/product-category/video-digital-microscope/) ▼
- [Microscope Camera \(https://bestamada.com/product-category/microscope-camera/\)](https://bestamada.com/product-category/microscope-camera/) ▼
- [Astronomy Camera \(https://bestamada.com/product-category/astronomy-camera/\)](https://bestamada.com/product-category/astronomy-camera/) ▼
- [Microscope Accessory \(https://bestamada.com/product-category/microscope-accessory/\)](https://bestamada.com/product-category/microscope-accessory/) ▲
 - > [LCD Screen \(https://bestamada.com/product-category/microscope-accessory/lcd-screen/\)](https://bestamada.com/product-category/microscope-accessory/lcd-screen/)
 - > [LED Ring Light \(https://bestamada.com/product-category/microscope-accessory/led-ring-light/\)](https://bestamada.com/product-category/microscope-accessory/led-ring-light/)
 - > [Objectives \(https://bestamada.com/product-category/microscope-accessory/objectives/\)](https://bestamada.com/product-category/microscope-accessory/objectives/)
 - > [Heated Stage \(https://bestamada.com/product-category/microscope-accessory/heated-stage-microscope-accessory/\)](https://bestamada.com/product-category/microscope-accessory/heated-stage-microscope-accessory/)
 - > [Illuminator \(https://bestamada.com/product-category/microscope-accessory/illuminator-microscope-accessory/\)](https://bestamada.com/product-category/microscope-accessory/illuminator-microscope-accessory/)
- [Night Vision \(https://bestamada.com/product-category/night-vision/\)](https://bestamada.com/product-category/night-vision/)

CONTACT US

AMADA INSTRUMENT CO.,LIMITED

Email: sales@bestamada.com

Skype: [amadastella@hotmail.com](https://www.hotmail.com/amadastella)

Address: No.866, Nanpu Road, Yanjiang Street, Pukou District, Nanjing, China

SEARCH

© 2023 AMADA Microscope (https://bestamada.com/). All rights reserved

How can I help you?