



(https://www.qnw.com/wp-content/uploads/2018/06/A0_0.5mm.jpg)

ADAPT/Abs/0.5mm

Cuvette Adapter for a 0.5 mm Path Length Absorbance Cell

This product adapts a 0.5 x 10 mm cuvette to fit into a standard cuvette holder for passage of light through the 0.5-mm dimension. Insert this anodized aluminum spacer to properly locate the cuvette for absorption measurements, with the light passing through at a z-height between 8.5 to 15 mm.

[request a quote \(/contact-us?referrer=ADAPT/Abs/0.5mm\)](/contact-us?referrer=ADAPT/Abs/0.5mm)