# **GASP® INSTRUMENTS** – For Measuring Surface Stress in Tempered, Heat-Strengthened, and Annealed Glass



#### **GASP** Models

The GASP polarimeter is available in two basic models:

**GASP** - the standard model for flat surfaces. It can also be used for slightly curved surfaces (radius of curvature >500 mm).

**GASP-CS** - recommended for curved surfaces with a radius of curvature >200 mm.

Either of these models is offered with a choice of light sources. A low-power diode laser is standard and a highintensity fiberoptic light for darker glass is also available. Video GASP options replace the standard eyepiece with either a separate or built-in LCD video monitor.

NEW IN OCTOBER 2018! The <u>Auto-GASP2</u> measures and stores measurements automatically and digitally by replacing the LCD screen with a small embedded touchscreen computer (not for annealed glass).

\* The GASP may be used for verification of surface compression in production samples of safety glazing, but not for certification.

The GASP Grazing Angle Surface Polarimeter is used for obtaining quantitative, non-destructive measurements of residual surface stress (pre-stress) on the "tin side" of flat, soda-lime float glass. Suitable for in-plant or field testing, it provides fabricators and end users with an accurate and simple method to:

- Measure surface compression levels in heattreated architectural, structural, solar, and automotive glass to ensure required mechanical strength and fragmentation characteristics
- Reduce or eliminate the need for destructive testing for many types of glass products
- Improve process control and productivity through optimization of furnace parameters
- Assure proper annealing
- Comply with worldwide industry standards and test methods, including ASTM, GANA, and CE requirements\*

Models for borosilicate float glass available on special order.

#### GASP instrument packages include:

#### • GASP-STAND<sup>™</sup>

- Rechargeable batteries for battery-operated models
- Standard (1X) measuring wedge for heat-treated glass, high-sensitivity (2X) measuring wedge for annealed glass, or extended range (0.5X) measuring wedge for very highly tempered glass.
- GASP index matching fluid (4 oz)
- Portable UV light (tin side detector)
- CAL-PLATE<sup>™</sup> for instrument verification
- Operator manual with calibration chart and certification documents
- Heavy-duty, instrument-quality carrying case with


Strainoptics logo

# **Strainoptics**

# **GASP® INSTRUMENTS** – For Measuring Surface Stress in Tempered, Heat-Strengthened, and Annealed Glass







# Applications for GASP Measurements:

- Heat-Treated Glass
- Safety Glass
- Annealed Glass
- Solar Glass
- Automotive Glass




## Specifications (Soda-Lime Float Glass Model)

Light Source:	Diode Laser	Fiber Optic (White Light)
GASP or GASP-CS with 1X Standard Wedge		
Measuring Range:	0-180 MPa (0-25,000 psi)	0-90 MPa (0-13,000 psi)
Resolution (+/-):		
Tempered Glass:	3.4 MPa (500 psi)	3.4 MPa (500 psi)
Heat-Strengthened:	1.7 MPa (250 psi)	1.7 MPa (250 psi)
Annealed Glass:	0.75 MPa (100 psi)	0.75 MPa (100 psi)
GASP or GASP-CS with 2X Standard Wedge		
Measuring Range:	0-84 MPa (0-12,000 psi)	0-35 MPa (0-5,000 psi)
Resolution (+/-):		
Annealed Glass:	0.5 MPa (75 psi)	

# **Strainoptics**

### How the GASP® Polarimeter Works




The GASP surface polarimeter is based on photoelastic test methods, using light rays traveling along the glass surface. The operation schematic is shown below. In use, the operator places a drop of index matching fluid on the tin side of soda-lime float glass) to ensure optical contact. The instrument is placed with its prism surfaces on the fluid, such that light travels through the entrance prism at a critical angle  $i_{c_1}$  enters the top surface of the glass and propagates parallel to the surface for a distance before emerging at a critical angle into the exit prism and up toward the eyepiece.

The surface stress introduces a photoelastic retardation R that increases linearly along the path 1-2. A quartz wedge (Babinet) compensator, containing a tight set of straight fringes, is placed on the path of the exit beam. The change in retardation,  $\Delta R$ , from 1 to 2, produces a tilt of the fringes at an angle  $\alpha$ , which is viewed through the GASP eyepiece. A dual reticle also appears in the eyepiece, which is rotated by the operator to match the fringe angle. The angle of the reticle lines is easily read by the operator and converted to a stress reading (psi, MPa). A calibration chart provides the surface stress measurement for each angle reading. The higher the angle, the higher the surface stress. Left-leaning lines indicate compression; right-leaning lines indicate tension (The opposite is true for the Video- and Auto-GASP due to image inversion by the camera optics).

## **Applications**

**Tempered (Toughened) Glass.** The strength of tempered glass is created by a heating and quenching process which creates a surface layer of compressive stresses, offsetting any tension caused by wind pressure, thermal shock, impact or other applied forces. ASTM C1048, EN12150-1 and other specifications require a minimum level of surface compression for glass to be classified as "Fully Tempered". While higher surface compression assures glass strength, the tempering process also creates tensile stress in the glass



mid-plane (see figure) which should also be controlled. If the tensile stress is too high, the glass may spontaneously rupture if it contains certain inclusions or defects. For this reason, an upper stress limit should be established to avoid potentially serious problems.

**Safety Glass.** "Safety" glass is strong, and it breaks into small, relatively harmless fragments. The surface stress in safety glass is typically above 15,000 psi (100 MPa). Break pattern testing is destructive and imprecise, and can result in substantial production loss if the results are not satisfactory. As with fully tempered glass, spontaneous breakage is known to develop in safety glass, with even larger financial losses. To optimize furnace settings, ensure conformance to specifications and avoid under- or over-stressing, safety glass should be frequently tested with the GASP.

*Heat-Strengthened Glass.* Heat-strengthened glass is stronger than annealed glass, but does not break into small fragments like safety glass. This characteristic is desirable when "fallout resistance" is required, such as for exterior glass in high story buildings. Surface stress in heat-strengthened glass must fall within narrow limits, specified by ASTM C1048, EN1863-1 and related standards. Fragmentation testing is not practical because the break pattern is very unpredictable, making the GASP surface polarimeter the most reliable way to test heat-strengthened glass for conformance to industry specifications.

Annealed and Low-Stress Glass. Non-destructive measurements of surface stress in annealed and low-stress glasses can be measured using a GASP instrument equipped with a high sensitivity wedge. In bent glass and in laminated automotive windscreens, the surface stresses are higher than in annealed glass and should be tightly controlled to remain within limits and detect areas of undesirable surface tension caused by bending.

**Solar Glass**. Manufacturers supplying the solar glass industry use the GASP surface polarimeter to ensure that both cover glasses and substrate glasses conform to their customer's specifications. Solar panel fabricators use it for incoming QC for the same reason. Non-uniform stresses in glass used for solar applications can cause a range of problems, ranging from degraded efficiency, poor impact resistance and mechanical strength, to lamination and assembly issues that can cause expensive field failures.

Note: This instrument is not suitable for the following types of glass: chemically-strengthened, patterned (rolled), low transmittance (<25% LTA), low tin, or coated on the tin side. For these applications, Strainoptics may be able to offer an alternative means of stress measurement. Please inquire.

# **Strainoptics**

# LCD-GASP<sup>™</sup> and Auto-GASP2<sup>™</sup>

- The LCD-GASP features a miniature CCD camera and a built-in 3.5" LCD video display. This simple-to-use instrument is more convenient than the Laser-GASP – just as portable & much easier to view. It can be viewed by multiple users at once, can be photographed for digital storage & greatly reduces operator fatigue when frequent measurements are required.
- NEW IN OCTOBER 2018!! The Auto-GASP2 (shown at right) makes . it possible to calculate surface stress in heat-strengthened or tempered glass automatically. The LCD screen is replaced by a small embedded touchscreen computer that calculates and stores measurements automatically in the field. Users have the ability to generate custom reports for their specific application and the unit includes a pyrometer for glass temperature measurement.
- Both LCD-GASPs and Auto-GASPs can be sold with a vertical attachment (shown at right) that holds the instrument in place against vertically oriented glass.

### Calibration and Certification

Each GASP instrument is factory calibrated and comes with a certificate of traceable calibration according to ASTM Procedure C1377. Strainoptics offers annual or periodic recalibration services as required. A certified CAL-PLATE is supplied with each complete GASP system to enable customers to self-certify their instrument where possible. A CAL-PLATE and certificate of calibration are shown at left.

# **Testing and Training Services**

Surface stress, edge stress, and other laboratory residual stress testing services are available from Strainoptics using equipment and test methods in accordance with ASTM and NIST standards. Strainoptics also provides training programs free to customers at our facility in North Wales, PA, or on a fee basis at a customer's location.

## **Other Strainoptics Products**

In addition to the GASP surface polarimeter, Strainoptics manufactures a complete range of manually operated and PC-based instrumentation for glass manufacturers and fabricators. These include on-line stress scanners for float glass production, visual and automatic edge stress meters, laboratory polarimeters and polarizing microscopes for analyzing stress distribution, specialized instruments for measuring stress and light transmission in automotive glass, roller wave gauges for measuring reflective distortion in architectural tempered glass, simple strain viewers (polariscopes) for visual inspection using photoelastic evaluation, and UV tin side detectors. Custom inquiries are always welcome. For more information, please visit our website or call.



 Strainoptics · 108 W. Montgomery Ave. · North Wales, PA 19454 USA · Tel: 215.661.0100 Fax: 215.699.7028 stress@strainoptics.com www.strainoptics.com





