

LOTIS TII LS-2136 laser is a high repetition rate Q-switched Nd:YAG laser emitting at the fundamental (1064 nm) and second (532 nm) harmonic.

The telescopic stable resonator has given the benefits of uniform beam quality, high energy and low beam divergence. The intracavity mode controlling telescope compensates the thermal lensing of the Nd:YAG rod and limits the irreducible beam divergence of laser by decreasing the transverse mode content of the beam.

There is no need for external water supply since the cooling system is totally self-contained with water-to-air heat exchanger.


The digital display remote control can be programmed to run in either auto or manual modes. It gives you fingertip control of all laser functions.

## **Specification**

Parameter		Value
Energy, mJ	1064 / 532 / 355 / 266 nm	140 / 75 / 25* / 18*
Pulse duration (FWHM at 1064 nm), ns		15–18
Pulse repetion rate, Hz		1–50
Beam divergence (full angle for 86 % of energy), mrad		0.7
Beam diameter, mm		≤5.0
Jitter**, ns		±1.5
Energy stability*** (1064 nm), %		±3.0
Size L x W x H, mm (Weight,	kg) Laser head Power supply Cooling system Remote control	815 x 206 x 136 (21.0) 446 x 449 x 177 (20.0) 446 x 449 x 266 (23.0) 105 x 175 (0.5)
Power requirements		Single phase, 220±20 V, 50–60 Hz, 1500 W

<sup>\*</sup> with Harmonic Generator Assembly HG-TF

<sup>\*\*\*</sup> shot to shot for 99% of pulses



For more information about LOTIS TII and its products visit www.lotis-tii.com

Copyright @ 2006 LOTIS TII Ltd. All rights reserved. LOTIS TII, the LOTIS TII logo are trademarks of LOTIS TII Ltd. All technical parameters are based on LOTIS TIII's standard testing methods.Subject to change without notice. This material is provided for informational purpose only. Brochure design by Applied Systems Ltd. www.appsys.net

<sup>\*\*</sup> with respect to external trigger of Q-switch