




355nm Expanders



Article number	Magnification Factor	design wavelength [nm]	max. input beam-Ø [mm]	clear output [mm]	Divergence Adjustable	total transmission [%]	mounting thread
QCM020-355	2x	355	6.0	31.0	✓	98	M30x1
QCM030-355	3x	355	6.0	31.0	✓	98	M30x1
QCM040-355	4x	355	6.0	31.0	✓	98	M30x1
QCM050-355	5x	355	5.5	31.0	✓	98	M30x1
QCM060-355	6x	355	4.0	31.0	✓	98	M30x1
QCM070-355	7x	355	4.0	31.0	✓	98	M30x1
QCM080-355	8x	355	3.5	31.0	✓	98	M30x1
QCM090-355	9x	355	3.0	31.0	✓	98	M30x1
QCM100-355	10x	355	2.5	31.0	✓	98	M30x1
QCM120-355	12x	355	2.2	31.0	✓	98	M30x1
QCM150-355	15x	355	1.8	31.0	✓	98	M30x1
QCM200-355	20x	355	1.4	31.0	✓	98	M30x1