



(http://www.ytoptics.com/)


Home (http://www.ytoptics.com/) About us (http://www.ytoptics.com/aboutus\_131.html)

Products (http://www.ytoptics.com/products.html)

Capability (http://www.ytoptics.com/capability.html) News (http://www.ytoptics.com/news.html)

Marketing (http://www.ytoptics.com/capability\_810.html)

Contact us (http://www.ytoptics.com/contact.html)

Products Category 	
Lens >	(http://www.ytoptics.com/lens.html)
Plano-Concave Lens >	(http://www.ytoptics.com/lens/plano-concave-lens.html)
Plano-Convex Lens >	(http://www.ytoptics.com/lens/plano-convex-lens.html)
Double-Concave Lens >	(http://www.ytoptics.com/lens/double-concave-lens.html)
Double-convex lens >	(http://www.ytoptics.com/lens/double-convex-lens.html)
Meniscus Lens >	(http://www.ytoptics.com/lens/meniscus-lens.html)
Achromatic Lens >	(http://www.ytoptics.com/lens/achromatic-lens.html)
<b>Triplet Lens</b> >	(http://www.ytoptics.com/lens/triplet-lens.html)
Rod Lens >	(http://www.ytoptics.com/lens/rod_lens.html)
Half Balls >	(http://www.ytoptics.com/lens/half_balls.html)
Cylindrical lens >	(http://www.ytoptics.com/lens/cylindrical_lens.html)
Balls >	(http://www.ytoptics.com/lens/balls.html)
Prisms >	(http://www.ytoptics.com/prisms.html)
Windows >	(http://www.ytoptics.com/windows.html)
Mirrors >	(http://www.ytoptics.com/mirrors.html)
Filters >	(http://www.ytoptics.com/filters.html)
Infrared Optics >	

[http://www.ytoptics.com/infrared\\_optics.html](http://www.ytoptics.com/infrared_optics.html)  
<http://www.ytoptics.com/coating.html>


### Contact us

Email: [admin@ytoptics.com](mailto:admin@ytoptics.com) (<mailto:admin@ytoptics.com>)

Tel: 86-431-87911611

Add: Building No.1,  
YuanChuangYueFu, Qiche Zone,  
Changchun, P.R. China(130000)

[Home \(http://www.ytoptics.com/\)](http://www.ytoptics.com/) > [Products \(http://www.ytoptics.com/products.html\)](http://www.ytoptics.com/products.html) > [Lens \(http://www.ytoptics.com/lens.html\)](http://www.ytoptics.com/lens.html)



## Triplet Lens

A triplet lens is cemented by one piece of crown glass with low refractive index and two piece of flint glass with high refractive index, normally the cemented lens can eliminate spherical chromatic aberration of axial direction. Because the design of these lenses are complete symmetrical, so they can be used by changing-over. The commonly used materials include crown glass and flint glass.

Share this: [f](#) [t](#) [in](#) [g+](#) [v](#)

[Inquiry Now](#)

### Product Description

**Specifications:**

- Materials: Three kinds of optical glass
- Diameter: 1.5—300mm
- Diameter Tolerance: +/-0.02 mm
- Thickness Tolerance: 0 +/-0.02mm
- Centring Error < 3 Arc minute
- Surface Quality: 20—10
- Surface Figure:  $\lambda/10 @ 633nm$
- Clear Aperture: 90%
- Coating: Specified by customers