

PRODUCT DATASHEET

ClearView® db Process Analyzer

VIS-NIR - Dual-Beam Photometer





Real-time

Configurable

Continuous PAT

- Color ASTM or Saybolt color in fuels
- OH (hydroxyl) number for polymer reaction end point
- Water content in solvents
- Haze in diesel fuel with turbidity option
- NaOH in water

Our ClearView[®] db photometer is the first commercially available true dual-beam filter photometer. A primary attraction of any photometric analyzer is its low cost; however, the compromise is usually performance. We have dramatically improved photometer performance by adding our unique dual-beam optics, which provides long term, stable operation. The flexible configurations of the ClearView db also meet many online analysis requirements for liquid and gas process streams.

ClearView db Benefits


- Stable dual-beam design decreases drift due to lamp aging yielding long-term performance
- Several enclosure options means lowest installation costs
- Six filter positions make multi-parameter analysis a possibility
- Optional second sample channel for lower cost per sample point
- Optional turbidity monitoring
- Compatible with a wide range of flow cells and insertion probes
- Low maintenance
- Long life Tungsten-Halogen Lamp (>4000 hours typical)
- Dual-beam performance lengthens time between required probe cleanings

Principle of Operation

Photometry is fundamentally the measurement of the intensity of light. Observable on many levels, changes in light intensity occur as a result of interactions with different materials. Further, the Beer-Lambert Law describes a useful relationship between light and matter. Matter absorbs light in measurable amounts at specific wavelengths. The degree of absorption correlates to the concentration of matter that is exposed to the light across a known optical distance, or pathlength. Thus, chemical concentrations and physical characteristics of a process stream sample can be accurately analyzed. Effective analyzer design permits this principle to be taken online, powerfully exploiting the science and achieving a high level of process control. Each successful ClearView db application is defined by the calibration. The calibration consists of absorption data corresponding to analytical values that describe the state of the process stream. Wavelengths specified for the application are represented by filters installed in the photometer. If and when changes occur in the process, the ClearView db measurements reflect this instantaneously.

Complete Analyzer System

The ClearView db is a complete analytical system comprised of three main components: 1) the photometer, 2) the fiber optic cables, and 3) the sample interface. The photometer both transmits the source light and quantifies the light that was not absorbed by the sample. Optical grade fiber cables are used to carry the light from the photometer to the sample and back. Using high performance fiber cables permits the sample interface to be located up to 100 meters from the photometer. Often the success of an analyzer hinges on the proper selection of the sample interface. The ClearView db is compatible with the large selection of our rugged and efficient sample interfaces. Now photometry is an option in even the harshest environments.



Specifications	
Design:	Fiber Optic Dual-Beam Photometer
No. of Channels:	1 Sample Channel, optional 2nd Sample Channel, optional Turbidity Monitoring for 1st Channel only
Number of Detectors/Filters:	2 – 6, any combination of detector types except 3 xInGaAs max
Filters:	As per customer requirements, max 6 individual filters
Detector Types:	Si (450 nm – 1050 nm) InGaAs (800 – 1650 nm) xInGaAs (1000 – 2150 nm, TE cooled), max 3
Light Source:	Tungsten-Halogen, >4000 hours typical
Spectral Range:	450 nm to 2150 nm
Photometric Noise:	<50 μAU 450-2100 nm 1 minute rms
Photometric Drift:	<500 μAU rms/ °C
Wavelength Drift:	Property of Filter
Response Time:	1 second, minimum. User settable
Fiber Size:	400, 500, or 600 μm diameter, single strand
Fiber Type Fused Silica:	Ultra Low-OH (optimum range: 450 nm – 2150 nm)
Fiber Connectors:	SMA 905
Outputs (analog):	Up to 6 for a 1 Channel Unit. Up to 4 per Channel for a 2 Channel Unit 4 – 20 mA, customer powered
Outputs (discreet):	Up to 6 for a 1 Channel Unit. Up to 4 per Channel for a 2 Channel Unit Contact closures
Inputs (analog):	4 (optional) 4 – 20 mA, isolated grounds
Local Display:	LCD Touch Screen, color QVGA
Communications:	Ethernet (TCP Modbus) standard
Enclosures:	General Purpose NEMA 4 Class I Division 2, Z-Purge, NEMA 4x Class I Division 1, IECEx, ATEX
Power:	24 VDC, 3 A
Environmental:	0 – 45°C, 0 – 90%, sun and rain sheltered
Dimensions: (H x W x D)	GP – 14"x 12"x 6" [36 cm x 31 cm x 15 cm] CID2 – 16"x 20"x 6" [41 cm x 51 cm x 15 cm] Explosion proof – 16"x 17"x 10" [41 cm x 43 cm x 26 cm]



GAIN REAL-TIME INSIGHT INTO YOUR PROCESS

Process Insights manufactures and delivers premium sensors, monitors, detectors, analyzers, instrumentation, and software that are mission-critical to keep your operations, personnel, and the environment safe – every day across the globe.

Get the most reliable, precision analytical technologies available on the market today. We will work to match your needs and budget, and provide the optimal, and most stable process analysis solution for your application.

CENTERS OF EXCELLENCE | PROVIDING PROVEN SOLUTIONS

Process Insights is committed to solving our customers' most complex analytical, process, and measurement challenges everyday.

Process Insights - The Americas

4140 World Houston Parkway Suite 180, Houston, TX 77032, USA +1 713 947 9591

Process Insights - EMEA

ATRICOM, Lyoner Strasse 15, 60528 Frankfurt, Germany +49 69 20436910

Process Insights - APAC

Wujiang Economic and Technology, Development Zone, No. 258 Yi He Road, 215200 Suzhou, Jiangsu Province, China +86 400 086 0106

For a complete range of products, applications, systems, and service options, please contact us at: info@process-insights.com

For a complete list of sales & manufacturing sites, please visit: https://www.process-insights.com/about-us/locations/

COSA Xentaur, Tiger Optics, Extrel, Alpha Omega Instruments, ATOM Instrument, MBW Calibration, MGA, Guided Wave, ANALECT and LAR TOC Leader are trademarks of Process Insights, Inc.



www.process-insights.com Copyright © 2023 Process Insights, Inc. All Rights Reserved.